



TYPICAL BASELINE OHMIC VALUES (ON FLOAT)

BATTERY TYPE	BASELINE OHMIC VALUES ON FLOAT			
	MIDTRONICS** (SIEMEN'S)	ALBER CELLCORDER (MILLI-OHMS)	BIDDLE BITE 2 (MILLI-OHMS)	BIDDLE MBITE (MILLI-OHMS)
CTC240	2042	3.236	2.618	2.837

- The above data are typical results and do not form a specification.
- Values are subject to change without notification.
- These values are not to be used to determine warranty claims.

** = Midtronics Meters include: Micro Celltron CTM-100
Celltron Advance CTA-2000
Celltron Ultra CTU-6000

- For batteries not listed contact East Penn Manufacturing.

Suspect ohmic values should be confirmed with a discharge test to determine the true capacity. Reference values stored in an ohmic meter must agree with the above tables for best results. Testers with pass/fail modes must use algorithms based on these reference values; although, a more thorough method of testing is recommended.

DISTRIBUTED BY:



East Penn Manufacturing Co.

Lyon Station, PA 19536-0147

Phone: 610-682-6361 Fax: 610-682-4781

www.dekabatteries.com

E.P.M. Form No. 2729 Rev. 9/23 © 2023 by EPM Printed in U.S.A.

All data subject to change without notice. No part of this document may be copied or reproduced, electronically or mechanically, without written permission from the company.